




WHITE PAPERS

& APPLICATION NOTES



DOWNLOAD FREE WHITE PAPERS & APPLICATION NOTES



Comparing CCD vs. CMOS Sensor Performance for Pixel-Level Display Measurement

Imaging systems rely on sensors to accurately interpret light as photometric data and enable evaluation of displays. This paper discusses properties of today's high-resolution sensors used for image-based photometric display testing, and examines measurement examples to compare sensor type (CCD versus CMOS), pixel size, and signal-to-noise ratio (SNR), and the effect of these properties on the accuracy and repeatability of data for pixel-level display measurement.

[DOWNLOAD NOW](#)

Sponsored by



More White Papers from this Sponsor

- Optimizing Imaging: Resolution & Dynamic Range
- Five Signs that a Photometry-Based Imaging System is the Right Choice for Your Inspection Application
- Resolution and Dynamic Range: How These Critical CCD Specifications Impact Imaging System Performance

PHOTONICS MEDIA

Visit Photonics Media to download other white papers and learn more about the latest developments in lasers, imaging, optics, biophotonics, machine vision, spectroscopy, microscopy, photovoltaics and more.

www.photonics.com/WhitePapers.aspx

We respect your time and privacy. You are receiving this email because you are a Photonics Media subscriber, and/or a member of our website, Photonics.com. You may use the links below to manage your subscriptions or contact us.

Questions: info@photonics.com

[Unsubscribe](#) | [Subscribe](#) | [Subscriptions](#) | [Privacy Policy](#) | [Terms and Conditions of Use](#)

Photonics Media, 100 West St., PO Box 4949, Pittsfield, MA 01202-4949

© 1996 - 2019 Laurin Publishing. All rights reserved. Photonics.com is Registered with the U.S. Patent & Trademark Office. Reproduction in whole or in part without permission is prohibited.