

PHOTONICS spectra®

PRODUCT SPOTLIGHT



The Easy Way to Upgrade Your Spectrometer

Optical fiber switches are the perfect solution to analyze different light sources with only one spectrometer. By utilizing multiple channels of the detector system at the same time, the light quality remains high while costs are low. Controlled by piezoelectric actuators light can be switched within milliseconds, while the insertion loss is around 1 dB. The fiber switches can be equipped with fiber core diameters from 50 μm up to 600 μm .

Download the data sheet for more information.

[Download Now](#)

We respect your time and privacy. You are receiving this email because you are a Photonics Spectra magazine subscriber. You may use the links below to manage your subscriptions or contact us.

Questions: info@photonics.com

[Unsubscribe](#) | [Subscribe](#) | [Subscriptions](#) | [Privacy Policy](#) | [Terms and Conditions of Use](#)

Photonics Media, 100 West St., PO Box 4949, Pittsfield, MA 01202-4949

© 1996 - 2021 Laurin Publishing. All rights reserved. Photonics.com is Registered with the U.S. Patent & Trademark Office. Reproduction in whole or in part without permission is prohibited.



LAURIN PUBLISHING

PHOTONICS MEDIA