

TruTag Hyperspectral Imaging

Model 4100H Hyperspectral Camera

HIGHLIGHTS

- » Fully autonomous high-resolution handheld hyperspectral camera
- » Down to 2 second acquisition
- » Visible to NIR (400-1,000 nm)
- » Up to 550 spectral bands
- » 7 nm (FWHM)
- » Dynamically configurable spectral bands
- » Option for active illumination for ambient-independent spectra
- » Configuration real-time object identification
- » 160mm² field of view
- » Ergonomic design
- » 3.5" color touchscreen with simple user interface
- » Wi-Fi and GigE / USB 3.0 interface
- » 4 rechargeable Li-ion batteries



TruTag Technologies, Inc. has developed the world's first autonomous high-resolution handheld hyperspectral camera. The award-winning device delivers 2.3 Mpixel data cubes at up to 550 spectral bands in the visible and near-infrared wavelength ranges with as little as 2 seconds of acquisition. The device's embedded processor enables real-time object identification based on a priori information on objects of interest. It's built-in light source allows acquisition of repeatable, absolute reflectance spectra.

Simple Usage Flow

To use, just turn on the device and it is ready to use, Hyperspectral cubes are captured by simply making contact with the object and pressing the trigger. Once an acquisition is complete, the user can view a video of the hyperspectral cube or scroll to a specific spectral band. Touching any pixel in the image displays the spectrum of this pixel. The camera's lamp spectrum can be subtracted in case of active illumination.

Powered by TruTag's HySi Engine Technology

The Model 4100H Hyperspectral Camera is powered by TruTag's Hyperspectral Engine Technology. At its center is a tunable Fabry-Perot Interferometer, assembled at TruTag's manufacturing facility using a proprietary process. The device achieves nano-meter-range mechanical tolerances with zero defects, in a robust and cost-effective system. TruTag's proprietary algorithms enable high-speed, low-power operation. Its active illumination option enables repeatable, absolute spectra to be acquired by novices and amateurs alike.

Intuitive Graphical User Interface (GUI)

The imager provides an effortless imaging experience. Guided by an intuitive graphical interface and powered by TruTag's advanced acquisition and processing engine, the handheld imager can capture millions of spectra in just a few seconds. The scanned spectral range as well as the sensitivity of the camera can be software configured. The acquired data cube can be transferred to an external computer via a wireless or GigE / USB 3.0 connection.

Collaboration and Configurability Options

While the Model 4100 offers unprecedented performance for users in academia, industry, and the clinic, the camera has been designed in a modular fashion to allow for customization for specific applications. Spatial resolution, acquisition times, field of view, working distance and spectral range can be designed to customers' specifications.

TruTag Hyperspectral Imaging

Model 4100H Technical Specifications

TRUTAG ADVANTAGES

» Staring Hyperspectral Imaging

No mechanical scanning is required, resulting in a lower-cost, reliable system.

» Off-Sensor Spectral Filtering

Decoupling the spectral filtering from the image sensor enables high spatial resolution.

» True Hyperspectral Imaging

Unlike color-filter arrays, with the TruTag solution, there is no trade-off between number of spectral bands and effective spatial resolution.

» Customizable

TruTags will work with strategic partner to optimize camera performance for specific application and will consider OEM models.

Mechanical

Dimensions (LxWxH)	230 mm x 260 mm x 105 mm (9.0" x 10.2" x 4.1")
Weight	1.6 kg (3.5 lb)

Electrical

Input Voltage	19 V \pm 5%
Operating Power	15 W
Batteries	4 rechargeable Li-ion
Battery-Run Operating Time	3.5 hours
Acquisitions per Battery Charge	>120
Data Interfaces	GigE or USB 3.0

Environmental

Operating Temperature	0°C to 40°C (32°F to 104°F) (Non-condensing)
Humidity	5% to 95% relative humidity, non-condensing
Ambient Light Levels	0-75,000 Lux (direct sunlight)

Scan Performance

Field of View	160mm ² area acquisition
Spatial Resolution	2.3 MP
Spectral Range	400 – 1,000 nm
Max Number of Spectral Bands	550
Spectral Resolution	7 nm (FWHM)
Illumination	Active (built-in) or Passive
Working Distance	Contact
Scan Angle	Perpendicular to object

TRUTAG TECHNOLOGIES, INC.

2200 Powell Street, Suite 1035
Emeryville, California 94608
+1 (808) TRU-TAGS
www.TruTags.com